

**Part Number :** [191210006](#)

**Product Description :** InsulKrimp Flanged Spade Tongue Terminal for 22-18 AWG Wire, Stud Size 6 (M3.5), Length 19.84mm, Mylar Tape Carrier

**Series Number :** 19121

**Status :** Active

**Product Category :** Ring and Spade Terminals

**Engineering Part Number :** AA-215-06XT



---

## Documents and Resources

### Drawings

[191210006 sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications


[PS-19902-009-001.pdf](#)

[PS-19902-015-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### [Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	Ring and Spade Terminals
Series	19121
Description	InsulKrimp Flanged Spade Tongue Terminal for 22-18 AWG Wire, Stud Size 6 (M3.5), Length 19.84mm, Mylar Tape Carrier
Keyword	Spade Terminal, Spade Terminals
Product Name	InsulKrimp
Style	Spade
Type	Spade Connector, Metric Spade Connector
UPC	800753095243

### Agency

CSA	LR18689
UL	E32244

### Physical

Barrel Type	Closed
Flammability	94V-0

Insulation	PVC
Material - Plating Mating	Tin
Net Weight	0.649/g
Packaging Type	Adhesive Tape on Reel
Stud Size	6 (M3.5)
Wire Insulation Diameter	3.68mm
Wire Size (AWG)	18, 20, 22
Wire Size mm <sup>2</sup>	0.25-1.50

### Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

---

## Application Tooling

### Global

Description	Part Number
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	<u>192880023</u>
Mini-Mac Pneumatic Applicator for Ring and Spade Terminals, 22-18 AWG	<u>638851300</u>

---

This document was generated on Jun 10, 2026