

# Neris

## Tri Band Internal GSM PCB Antenna

### Features

- ◆ Groundplane Independent
- ◆ Covers 900/1800 and 1900 MHz bands
- ◆ Various cable/connector options
- ◆ Ideal for fixed and mobile terminals

### Specifications

Specifications	
Radiating element	1/2 Wave Element
Frequency range	900/1800 and 1900 MHz
Peak gain	1.0 dBi
Polarisation	Linear
Return loss	-8 dB
Power rating	10W
Cable / Connector	Various including MMCX, U.FL, SMA
Dimensions	81 x 21mm

### Popular Ordering Options

FNER35001-MR-16	Neris with 160mm RG-178 and MMCX Connector
FNER35001-UF-10	Neris with 100mm cable and U.FL Connector



Specifications subject to change without notice.

5 Little Balmer  
Buckingham Industrial Park  
Buckingham  
MK18 1TF  
UK

Tel: +44 (0)1280 824055  
Fax: +44 (0)1280 817179  
Email: [sales@ead-ltd.com](mailto:sales@ead-ltd.com)  
Web: [www.ead-ltd.com](http://www.ead-ltd.com)

## Neris| Tri Band GSM Internal PCB Antenna

### Return Loss



Specifications subject to change without notice.

5 Little Balmer  
Buckingham Industrial Park  
Buckingham  
MK18 1TF  
UK

Tel: +44 (0)1280 824055  
Fax: +44 (0)1280 817179  
Email: sales@ead-ltd.com  
Web: www.ead-ltd.com

**EAD**  
embedded antenna design ltd  
*Delivering Antenna Innovation*