


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NO.	MATERIAL	"A" +/- .062	"B" +/- .062	LABELS PER ROW	LABELS PER PKG.
N050X150CBT	GMC4	1.500 [ 38.1 ]	1.600 [ 40.6 ]	7	2500
N050X175CBT	GMC4	1.750 [ 44.5 ]	1.800 [ 45.7 ]	7	2500



CAD FILENAME/LAYERS  
100472JS\_C10296\_N050XNUMCBT\_00.PRT

PANDUIT CORP. TINLEY PARK, ILLINOIS

OPTIMUM N050X\*\*\*CBT  
THERMAL TRANSFER LABELS

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONAL TOLERANCES ARE:  
(.X) ± .12 (XXX) ± .025  
(.XX) ± .062 ANGLES ±

UNLESS OTHERWISE SPECIFIED,  
ALL DIMENSIONS ARE GIVEN  
IN INCHES, THIRD ANGLE PROJECTION.

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
1	7/9/09	RVU		GMC4 WAS GMC. ADD +/- .062. REMOVE NOTE 1. INCORRECT TOLERANCES.	5792	R		
0	10-1-04	RVU		DRAWING RELEASED.	0000	R		

DRAWN BY RVU	MAT'L:	SCALE NTS
DATE 10-1-04	SEE TABLE	DRAWING NO. C10296
CHK'D		DWG A SIZE