

YA25L2NT14

Flex Conductor Standard Barrel Narrow, 1/0 AWG, 1/4 in, 2.56 in L

[Image](#) | [Line Art](#) | [3D Model](#) | [Video](#) | [Customer Drawing](#)

 [Email Datasheet](#)

 [Print Datasheet](#)



Active

Specifications

Documents

Tools & Dies

Dimensional

General

Conductor(s)

Physical

Approvals / Certifications

Other Features

Dimensional

Tongue Angle	Straight
Length (in)	2.56
Barrell Style	Chamfered
Bolt Hole Size (in)	0.27
Barrel Type	Standard
Thickness	0.12
B Length (in)	0.88
Pad Width (in)	0.48
E - in	0.63
Strip Length	15/16

General

Number of Holes	2
Product Description	Flex Conductor Standard Barrel Narrow, 1/0 AWG, 1/4 in, 2.56 in L

Conductor(s)

Flex (Class G) Size - Range	N/A
Flex (Class H) Size - Range	N/A
Flex (Class I) Size - Range	N/A
Copper Solid Size (Range)	N/A
DLO Size (Range)	N/A
Copper Stranded (Range)	1/0

Physical

Type of Plating	Tin - Electro Plated
Bolt Hole Size	1/4
Color Code	Pink
Plated (Yes or No)	Y
Index Number	12
Product Material	Copper

Approvals / Certifications

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N

Other Features

UPC	7818102799777
-----	---------------