
1375189-1



SL110 Series Modular Jack, category 5e, T568A/T568B, shielded, 180° (rear) entry shield, black

OBSOLETE

This product was discontinued on: July 30, 2019

Replaced By:

2153448-4 AMP-TWIST SLX, 6S,GY	AMP-TWIST SLX Series Modular Jack, category 6, shielded , 4 Pair, without dust cover, gray
760238140 USL600-SHLD, GY	Uniprise SLX Series Modular Jack, category 6, shielded , 4 Pair, without dust cover, gray

Product Classification

Regional Availability	Asia | EMEA | Latin America | North America
Portfolio	NETCONNECT®
Product Type	Modular jack
Product Series	SL Series

General Specifications

ANSI/TIA Category	5e
Cable Type	Shielded
Color	Black
Conductor Type	Solid | Stranded
Integrated Dust Cover Type	None
Outlet Type	Standard
Termination Punchdowns, minimum	200 times
Termination Tool	SL Termination tool
Termination Type	IDC
Transmission Standards	ANSI/TIA-568-C.2 | ISO/IEC 11801 Class D

©2021 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: March 3, 2021

COMMSCOPE®

Downloaded from Arrow.com.

1375189-1

Wiring	T568A | T568B

Dimensions

Panel Cutout, recommended	14.78 x 20.07 mm (0.58 x 0.79 in)
Panel Thickness, recommended	1.6 mm | 0.063 in
Height	16.26 mm | 0.64 in
Width	14.48 mm | 0.57 in
Depth	30.48 mm | 1.2 in
Compatible Insulated Conductor Diameter, maximum	1.45 mm | 0.057 in
Contact Plating Thickness	1.27 µm
Compatible Conductor Gauge, solid	24–22 AWG
Compatible Conductor Gauge, stranded	26–24 AWG

Electrical Specifications

Safety Voltage Rating	150 Vac

Material Specifications

Contact Base Material	Beryllium copper
Contact Plating Material	Gold
Material Type	Polycarbonate

Mechanical Specifications

Plug Insertion Life, minimum	750 times
Plug Retention Force, minimum	89 N | 20.008 lbf

Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Flammability Rating	UL 94 V-0
Safety Standard	CSA | cUL

Packaging and Weights

Included	Strain relief cap
Packaging quantity	1
Packaging Type	Bag

©2021 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: March 3, 2021

COMMSCOPE®

Downloaded from Arrow.com.

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant



©2021 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: March 3, 2021

COMMSCOPE®

Downloaded from Arrow.com.