

## Snap-in markers - UC-EMP (27X15) - 0825439

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Snap-in markers, Sheet, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped into marker carrier, lettering field size: 27 x 15 mm, Number of individual labels: 8

### Your advantages

- ✓ The UC-EMP ... UniCard labeling range includes markers that can be fitted into existing CARRIER-EMP ... label frames
- ✓ The wide temperature range means that the labels can be used in control cabinets as well as the field
- ✓ The sheets provide space for including function texts
- ✓ The markers, which are supplied in uniform sheets, can be printed onto quickly and easily using the BLUEMARK LED
- ✓ The format automatically ensures printing with a high degree of positioning accuracy
- ✓ Labeling service: Phoenix Contact can custom-label all UniCard markers according to your requirements

RoHS

### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 046356 365505
GTIN	4046356365505
Weight per Piece (excluding packing)	12.000 g
Custom tariff number	39269097
Country of origin	Poland

### Technical data

#### Dimensions

Length (b)	15 mm
Width (a)	27 mm

# Snap-in markers - UC-EMP (27X15) - 0825439

## Technical data

### Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.

### General

Color	white
Components	free from silicone and halogen
Material	PA
Flammability rating according to UL 94	V2
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	8
Number of individual labels per row	2
Mounting type	snapped into marker carrier
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 2
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 2
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 2
Testing substances harmful to the wetting properties of lacquers (LABS conformity)	VW PV 3.10.7:2005-02
Result	Test passed
UV resistance	Following ISO 4892-2:2013-03
Result	Test passed
Test duration	96 h
Test for wipe resistance of inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Testing in a condensation changing climate in the presence of sulfur dioxide	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1,0 S
Cycles	2
Salt spray test	DIN EN 60068-2-11:2000-02
Result	Test passed

### Environmental Product Compliance

China RoHS	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"
------------	---

## Classifications

eCl@ss

eCl@ss 10.0.1	27400629
---------------	----------

## Snap-in markers - UC-EMP (27X15) - 0825439

### Classifications

#### eCl@ss

eCl@ss 11.0	27281106
eCl@ss 4.0	24190200
eCl@ss 4.1	24190200
eCl@ss 5.0	27149100
eCl@ss 5.1	27141100
eCl@ss 6.0	27149100
eCl@ss 7.0	27149129
eCl@ss 9.0	27400629

#### ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 6.0	EC001288
ETIM 7.0	EC001530

#### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

### Accessories

#### Accessories

#### Magazine

Magazine - P1 UC-MAG 6 - 5146121



Magazine, for CMS-P1-PLOTTER and PLOTMARK, for accommodating UC-EMP..., UC-EMLP...

## Snap-in markers - UC-EMP (27X15) - 0825439

### Accessories

#### Marker carriers

Marker carriers - CARRIER-EMP 22 (27X15) - 0827447



Marker carriers, black, unlabeled, mounting type: snapped, diameter: 22 mm, lettering field size: 27 x 15 mm

---

Marker carriers - CARRIER-EMLP 22 (27X15) - 0828986



Marker carriers, black, unlabeled, mounting type: screw, rivet, diameter: 22 mm, lettering field size: 27 x 15 mm

---

Marker carriers - CARRIER-EMP (27X15) - 0827451



Marker carriers, black, unlabeled, mounting type: screw, rivet, lettering field size: 27 x 15 mm

---

Marker carriers - CARRIER-EMP (1000X15) GY - 0829366



Profile, for screwing or riveting, 1000 mm long, for accommodating UC und US materials, height: 15 mm

---

Marker carriers - CARRIER-EMP (1000X15) TR - 0829530



Marker carriers, transparent, unlabeled, mounting type: screw, rivet, lettering field size: 1000 x 15 mm

---

## Snap-in markers - UC-EMP (27X15) - 0825439

### Accessories

Marker carriers - CARRIER/L-EMP (1000X15) GY - 0829559



Profile, self-adhesive, 1000 mm long, for accommodating UC and US materials, height: 15 mm

---

Marker carriers - CARRIER/L-EMP (1000X15) TR - 0829560



Profile, self-adhesive, 1000 mm long, for accommodating UC and US materials, height: 15 mm

---

### Printing system accessories

Ink cartridge - BLUEMARK CLED-FLUID-CARTR. - 5146662



Cartridge, for replacement, 20 ml UV color, black, including cleaning cartridge

---

Ink cartridge - BLUEMARK FLUID-CARTRIDGE - 5147421



Cartridge, for replacement, 28 ml UV color, black including cleaning cartridge

---

Ink cartridge - BM ID-CARTR. BK - 1044345



Replacement UV fluid, 23 ml, color: black

---

## Snap-in markers - UC-EMP (27X15) - 0825439

### Accessories

Ink cartridge - BM ID-CARTR. CY - 1044346



Replacement UV fluid, 23 ml, color: cyan

---

Ink cartridge - BM ID-CARTR. MA - 1044347



Replacement UV fluid, 23 ml, color: magenta

---

Ink cartridge - BM ID-CARTR. YE - 1044348



Replacement UV fluid, 23 ml, color: yellow

---