

Conductor marker carrier - PATG 5/18 - 0828059

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Conductor marker carrier, transparent, unlabeled, Mounting type: slide on, Cable diameter: 10-14 mm, Lettering field: 4 x 18 mm

The figure shows version

Why buy this product

- ✓ The corresponding UC-WMT ..., US-WMT ..., UCT-WMT ... and EMT ... insert labels are used for marking
- ✓ These conductor marking systems consist of marker carriers and insert labels
- ✓ The PATG ... collar is a captive marker carrier
- ✓ Can be used to mark conductors with a diameter of 0.6 ... 50 mm

RoHS

Key Commercial Data

Packing unit	1 STK
Minimum order quantity	200 STK
GTIN	 4 046356 467025
GTIN	4046356467025
Weight per Piece (excluding packing)	0.800 g
Custom tariff number	39269097
Country of origin	Germany

Technical data

Dimensions

Width (a)	18 mm
Cable diameter	10 mm ... 14 mm

Ambient conditions

Ambient temperature (operation)	-50 °C ... 80 °C
---------------------------------	------------------

Conductor marker carrier - PATG 5/18 - 0828059

Technical data

General

Color	transparent
Components	Silicone-free
Flammability rating according to UL 94	V0
Material	PVC
RoHS compliant	Yes
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Marking mounting type	slide on

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Environmental Product Compliance

REACH SVHC	DOT 15571-58-1
------------	----------------