

1


2

3

4

5

RoHS Compliant



Notes:

1.P2 Waterproof Rate:IP67


2.Electrical Characteristics:

Current Rating:1A

Voltage Rating:30V


PIN OUT:

P1		P2
1	Red(24AWG)	1
2	White(28AWG)	2
3	Green(28AWG)	3
4	Black(24AWG)	4
Shell	Drain+Brain	Shell

Recommended Panel Cut-Out
Thickness 3.5Max.

P/N	L
107-1023-BL-00050	500±30
107-1023-BL-00100	1000±30
107-1023-BL-00150	1500±30
107-1023-BL-00200	2000±40

ITEM	DESCRIPTION	MATERIAL	PLATING & COLOR	Q'TY
1	USB A Jack	USB2.0 Female	Gold Plated 30u"	1
2	Housing	PPE	Black	1
3	Screw Nut	PPE	Black	1
4	Gasket	EPDM	Black	1
5	PCB	FR-4	Green	1
6	Heat Shrink Tube	OD:1.0 L=15	Black	1
7	Heat Shrink Tube	OD:5.0 L=15	Black	1
8	Cable	UL2725 24AWG*2C+28AWG*1P+ADB OD:4.7	Black(PVC Jacket)	1
9	Cap	PPE	Black	1
10	Chain	TPU	Black	1

				DRAWN:	GENERAL TOLERANCE: X=±5 .X=±0.5 .XX=±0.3	CnC Tech Industrial Cable and Connector Technology	
				CHECKED:	UNIT: MM SCALE:1:1		
B				APPROVAL:	SHEET: 1 / 1	DESCRIPTION: WATERPROOF USB FEMALE CABLE ASSEMBLY	
A	11-Jul-2019				PROJECTION: 	PART NO: 107-1023-BL-00XXX	
REV	DATE	FILE	BY			SIZE A4	