Part Number : 22552383
Product Description : 2.54mm Pitch SL Crimp Housing, Dual Row, Version C, Back Ribs, 38 Circuits, Black
Series Number : 70450
Status : Active
Product Category : Connector Housings
Engineering Part Number : 70450-0117



Documents and Resources

Drawings

022552383_sd.pdf

PK-70450-100-001.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-70058-001.pdf

PS-70400-001.pdf

TS-70058-001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Downloaded from Arrow.com.

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	70450
Description	2.54mm Pitch SL Crimp Housing, Dual Row, Version C, Back Ribs, 38 Circuits, Black
Application	Signal, Wire-to-Board
Comments	Version C
Product Name	SL
UPC	800753778566

Agency

CSA	LR19980
UL	E29179

Physical

Circuits (maximum)	38
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No

Downloaded from Arrow.com.

Material - Resin	Polyester
Net Weight	3.262/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Stackable	Yes
Temperature Range - Operating	-40° to +105°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
C-Grid Right-Angle Dual Row Headers	70229
C-Grid Right-Angle, Dual Row, Low Profile Headers	70247
C-Grid Vertical Dual Row Breakaway Headers	70280
C-Grid Vertical, Dual Row, Low Profile Headers	70246

Use with Part(s)

Description	Part Number
SL Female Terminals	70058
SL Female Terminals	71851

Downloaded from Arrow.com.