

Quick Links

Cross reference

RoHS/LF P/N Search

Industry Standards

Alphabetical List

Documentation

3D model search

Customer drawing search

Multi Selection Search

Search by category

Start > Search=10134280-001LF* > 10134280-001LF

10134280-001LF

10134280-001LF : Earth SCREW Terminal Block E6



ACTIVE

RoHS Compliant

Distributor Stock

 [Print Datasheet](#)

FCI Brings You More

 > [Contact our sales/technical support](#)

 > [Sample request](#)

 Customer drawing

 Environmental Compliance Report

Specifications

Download document

General	Dimensional	Electrical	Physical	Approvals / Certifications	Mounting
General					
Pollution Degree	3				
Insulating Material Group	I				
Number of contacts (Total)	2				
Number of decks	Single				
Packaging	Pack				
Product Type	Earth Screw Terminal Blocks				
Attachment type (Board)	DIN Rail				
Dimensional					
Width	8 mm				
Conductor cross section solid (min-max)	0.50 / 6 sqmm				
Conductor cross section stranded (min-max)	0.50 / 6 sqmm				
Length (Overall)	58 mm				
Strip length (Wire)	max 12 mm				
Solid wire size (AWG)	22-8				
Height (Total)	44 mm				
Electrical					
Rated Surge Voltage	6kV				
Surge Voltage Category	III				
Physical					
Color (Housing)	Yellow/Green				
Installation Torque	0,8 Nm				
Flammability rating	UL 94 V-2				
Approvals / Certifications					
Approvals / Certifications	Kema EX				
Mounting					
Mounting style	Omega TH 35				

Disclaimer : The information above is for reference only. For more technical details, refer to product specification and application specification.

Downloaded from [Arrow.com](https://arrow.com).