



## Eaton Bussmann series EuroMag EM3675 terminal block

**EM367509**

**UPC:**051712908337

### Dimensions:

- **Height:** .394 IN
- **Length:** 1.772 IN
- **Width:** .315 IN

**Weight:**.1 LB

### Warranties:

- Eaton Selling Policy 25-000 generally applies with some exceptions. Drive products come with a standard 24 months from date of shipment and 36 months with Eaton certified start up all inclusive coverage parts labor and travel.

### Specifications:

- **Application:** industrial
- **Type:** 5.00 Centers
- **Voltage Rating:** 300 V
- **Number Of Poles:** Nine-pole
- **Operating Temperature:** -40° to 105°C
- **Wire Size:** #26-14 AWG Cu
- **Screw Size:** M2.6 zinc plated steel
- **Wire Range:** #14-26 AWG
- **Torque Rating:** 4 lb-in
- **Center Spacing:** 0.197 in
- **Recommended PCB Hole Diameter:** 0.055" (1.40mm)
- **Contact Material:** Tin plated brass
- **Housing Material:** UL rated 94V0 thermoplastic
- **Material:** Tin-plated brass

### Supporting documents:

- [Product Catalog](#)

**Certifications:**

- UL Recognized

**Product compliance:**

- CE Marked
- RoHS Compliant
- EU Directive 2002/95/EC Category 3 (4 of 5)

---

© 2016 Eaton. All rights reserved.