
Part Number : 191930014
Product Description : VersaKrimp Ring Tongue Terminal for 22-18 AWG Wire, Closed-Brazed Barrel, Stud Size 8 (M4), Carton
Series Number : 19193
Status : Active
Product Category : Ring and Spade Terminals
Engineering Part Number : AA-321-08



Documents and Resources

Drawings

191930014_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-19902-011-001.pdf

PS-19902-013-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

Downloaded from Arrow.com.

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19193
Description	VersaKrimp Ring Tongue Terminal for 22-18 AWG Wire, Closed-Brazed Barrel, Stud Size 8 (M4), Carton
Keyword	Ring Terminal, Ring Terminals
Product Name	VersaKrimp
Style	Ring
Type	Ring Terminal, Metric Ring Terminal
UPC	800755048964

Agency

CSA	LR18689
UL	E32244

Electrical

Voltage - Maximum	up to 35kV

Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Metal	Copper

Downloaded from Arrow.com.

Material - Plating Mating	Tin
Net Weight	0.520/g
Packaging Type	Carton
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Stud Size	8 (M4)
Temperature Range - Operating	-50° to +149°C
Termination Interface Style	Crimp or Compression
Wire Size (AWG)	18, 20, 22
Wire Size mm^2	0.25-1.50

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 22-10 AWG and 6.0mm^2 - 0.5mm^2	640030100
Crimp Head for the AT-200 Pneumatic Hand Tool	640070100
ServiceGrade Hand Crimp Tool - Ratchet	640160038

Downloaded from Arrow.com.