

## Han 10B Docking Frame IP67 fixed



Image is for illustration purposes only. Please refer to product description.

Part number	09 30 010 1710
Specification	Han 10B Docking Frame IP67 fixed
HARTING eCatalogue	<a href="https://harting.com/09300101710">https://harting.com/09300101710</a>

### Identification

Category	Accessories
Type of accessory	Docking frame

### Version

Size	10 B
Details	Pull-in-range x-axis: $\pm 1$ mm Pull-in-range y-axis: $\pm 1$ mm Pull-in-range z-axis: - 0.5 / +1 mm

### Technical characteristics

Mating cycles	$\geq 10,000$
Note on the mating cycles	Mating cycles with other HMC components
Degree of protection acc. to IEC 60529	IP65 / IP67

### Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (seal)	NBR
Material (accessories)	Stainless steel

### Commercial data

Packaging size	1
Net weight	234.4 g

## Commercial data

Country of origin	China
European customs tariff number	85389099
GTIN	5713140572348
eCl@ss	27440206 Module carrier frame for industrial connectors
ETIM	EC002312
UNSPSC 24.0	39121421