



Part Number : [1301110112](#)

Product Description : LED String Light, 2 Light Engines, 12/3 SJTW Cable, 28W, NEMA 5-15 Plug and Receptacle, 7.62m (25.0') Overall Length

Series Number : 130111

Status : Active

Product Category : Lamps and Lights

Engineering Number : 123JQ25-14W10515M



Documents & Resources

Drawings

[1301110112 sd.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Lamps and Lights
Series	130111
Description	LED String Light, 2 Light Engines, 12/3 SJTW Cable, 28W, NEMA 5-15 Plug and Receptacle, 7.62m (25.0') Overall Length
NEMA Configuration	NEMA 5-15
NEMA Rating	Wet Location
Product Name	LED String Light
Type	String Lights
UPC	78172561011

Agency

UL	E112216
----	---------

Electrical

Lamp Wattage - Maximum	14W
Lumens	4256
On/Off Switch	No
Voltage (Fixture) - Maximum	125V

Physical

Bulb Type	LED - 5000K
Cord Length - Primary	4.27m (14.0')
Cord Length - Secondary	0.305m (1.0')
Cord Type - Primary	12/3 SJTW
Cord Type - Secondary	12/3 SJTW
Depth	86.25mm (3.400")
Duty	Outdoor Use
Guard Included	No
Guard Type	N/A

Height	121.92mm (4.800")
Lamp Type	Integral LED
Length	7.62m (25.0')
Material - Globe	Translucent Polycarbonate
Mounting Style	Stringer
Outlet	Feed-Through
Packaging Type	Carton

This document was generated on Sep 18, 2025