

Test probes

PRUEF 2600



| Product | PRUEF 2600 |
|--|--|
| description | Test probe with shatter-proof insulating sleeve and slender stainless steel tip. Tip for penetration of oxide layers. 4 mm diameter brass socket connection. Connects with safety measuring leads. |
| operating instruction | BA464 |
| article-no. / *colour | <div> <div>●</div> <div>00</div> <div>black</div> </div> <div> <div>●</div> <div>01</div> <div>red</div> </div> |
| drawing | |
| | |
| technical data | |
| connection | unsprung socket 4 mm |
| rated voltage | AC/DC 1000 V |
| measurement cat. acc. to IEC 61010 | CAT III |
| rated current (consider derating curve) | 1 A |
| material socket | brass |
| housing material | PP |
| temperature range acc. To IEC61010 ⁽¹⁾ | -25 °C to +70 °C |
| flammability class acc. to UL 94 (only valid for basic material of housing) | HB |

⁽¹⁾ contact the manufacturer for applications at deviating temperature ranges
 stand: 21.06.2022

stand: 21.06.2022