




PRODUCT NO	SIZE	STYLE	DIM A	DIM B	DIM C
68751-X10	2 X 5	A	.78/19.81	.72/18.29	.400/10.16
-X14	2 X 7	C	.98/24.89	.92/23.37	.600/15.24
-X16	2 X 8	D	1.08/27.43	1.02/25.91	.700/17.78
-X20	2 X 10		1.28/32.51	1.22/30.99	.900/22.86
-X24	2 X 12		1.48/37.59	1.42/36.07	1.100/27.94
-X26	2 X 13		1.58/40.13	1.52/38.61	1.200/30.48
-X30	2 X 15		1.78/45.21	1.72/43.69	1.400/35.56
-X34	2 X 17		1.98/50.29	1.92/48.77	1.600/40.64
-X40	2 X 20		2.28/57.91	2.22/56.39	1.900/48.26
-X44	2 X 22		2.48/63.00	2.42/61.47	2.100/53.34
-X50	2 X 25		2.78/70.61	2.72/69.09	2.400/60.96
68751-X60	2 X 30	D	3.28/83.31	3.22/81.79	2.900/73.66

REVISIONS			
REV	DESCRIPTION	BY	DATE
B			

DASH	TERMINAL PLATING	PIN SHAPE	DIM D
-0XX	30μ"/.76μ Au / 50μ"/1.27μ Ni	RD	.105/2.67
-1XX	30μ"/.76μ GXT GOLD FLASH / 50μ"/1.27μ Ni	RD	.105/2.67
-2XX	30μ"/.76μ Au / 50μ"/1.27μ Ni	SD	.120/3.05
-3XX	30μ"/.76μ GXT GOLD FLASH / 50μ"/1.27μ Ni	SD	.120/3.05

SHEET INDEX		TITLE		CUSTOMER COPY		CODE IDENT		DATE		FCJ		www.fcjconnect.com	
SH NO 1				22536		6/2/92		6/2/92		TITLE		HEADER ASS'Y, SLIM LINE, 4 WALL, END LATCH	
MODEL		DO NOT SCALE DRAWING		TOLERANCE UNLESS OTHERWISE NOTED		DIN4MM		MATERIAL		DR		M. CLOUSER	
				.004/.01/.013						CHK		M. SHYK	
				.004/.005/.004/.12						ENGR		M. SHYK	
				.004/.005/.004/.004						APPR		M. SHYK	
TABULATION SHEETS REQUIRED		YES		INCH		MM		ANGLES		0° ±2°		SCALE SIZE DWS NO	
NO												8/1 D 68751 SHEET 3	

NOTE: This print is the property of and contains proprietary designs of the FCJ Company. No part of the design shown on this print may be used in any way without the written consent of FCJ ELECTRONICS, Inc. Eastford, CT.