

()

()



Amphenol
FCi

()

© 2016 AFci

()

D





Plating: 4 --> flash AU
Plating: 6 --> 0.76µ AU


Part number D50P24A*P*00LF

V--> Female screw UNC 4-40

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C01-8646-0000



PC card drilling dimensions
(after plating - thickness: 1.60 mm)
±0.10



Notes:

1) The nut can protrude above the surface of insulator but maintaining the footprint dimension 6.0±0.15 mm.

mat'l. code				surface		tolerance		projection	product family			
				ISO 1302	ISO 406	ISO 1101	ISO 1101		D-SUB			
ltr	ecn no	dr	date	tolerances unless otherwise specified				mm	title			
A		GM	16-10-2020	angles	linear				MALE DELTA-D 50 EUROPE			
				0°±x'				scale NTS	STRAIGHT SOLDER			
				dr	GREGAR M	16-10-2020		Amphenol FCi	dwg no		sheet 1 of 1	
				enr	GREGAR M	16-10-2020			10149461		A3	
				chr	SREERAJ KR	16-10-2020						
				appd	SANOJ P K	16-10-2020			type		Product Customer Drawing	
sheet index	revision	A										
	sheet	1										