



Connector Component			Connector Strip Dimension			Wire Spec.	Terminal ROJ & Strip		
Color	Component	Qty	Strip	ROJ	Color	SJT 18AWGX3C 105°C BLACK Length: 2000±50 mm	Strip	ROJ	Color
40P BK 90±5°A	IEC 320 C13 (LT-501(10A 250V))	1	7±1	20±3	Black		5⁄8" (16mm)	2" (50.8mm)	Black
Copper	computer power cord terminals	3	7±1	20±3	White		5⁄8" (16mm)	2" (50.8mm)	White
White	(501 Inner Body)	1	7±1	20±3	Green		5⁄8" (16mm)	2" (50.8mm)	Green

RHYTHM: (UL) E88231 SJT 3X18AWG(0.824mm²)
105°C 300V VW-1 CSA LL54496 SJT
3X18AWG(0.824mm²)105°C 300V VW-1
RHYTHM R

1. PLUG : NA
2. CONNECTOR : LT-501 IEC-60320 C13
3. CORD : SJT 18AWGX3C 105°C BLACK 2M
4. APPROVALS : UL, C-UL
5. Supplier for flexible cord : RHYTHM
6. Hi-Pot Test:2000v/1min<1mA>

	DESCRIPTION	DATE

DRAWER	Eric	DATE	20/10/17	P/N	800-1809-2-SJT0-BL-00200
APPROVE		REV.	0	Dr.No.	1091059
		比例	TOL.		±5mm
			ALL DIMENSIONS IN mm		

CnC Tech

Industrial Cable and Connector Technology