




Rev	AWO #	Description	Date	Appr
-		RELEASED	4/6/05	
A		REDRAWN	11/16/11	
B		REVISED SPEC.	1/8/13	

APPROVED: _____
DATE: _____ TITLE: _____



SPECIFICATIONS:

Material: Nylon 66, rated UL 94V-2
Insulator color: White
Electrical:
Operating voltage: 150 VAC max
Current rating: 2 Amp max
Insulation resistance: 1,000 Mohms min @ 500 VDC
Dielectric withstanding voltage: 800 VAC for 1 minute
Temperature Rating:
Operating temperature: -25°C to +85°C
Environmental:
Lead free, RoHS compliant



Positions: 2 thru 20
A = .079 [2.00] x No. of Spaces + .150 [3.80]
B = .079 [2.00] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]				ADAM TECH			
TOLERANCES: EXCEPT AS NOTED				909 Rahway Avenue, Union, NJ 07083			
INCHES				Phone: 908-687-5000 Fax: 908-687-5710			
Holes				.079 [2.00] CRIMP HOUSING			
.X	± .10	ØXX	± .10	LOW PROFILE, DUAL POLARIZED			
.XX	± .020	ØXXX	± .015				
.XXX	± .015	ØXXXX	± .010				
APPROVALS				TITLE			
DRAWN	SS	4/6/05	DATE	.079 [2.00] CRIMP HOUSING			
CHECKED				PART NO.			
APPROVED				2CH-C-XX			
REF:	S00016T	SCALE:	NTS	SHEET	1	OF	1