Part Number : 192030099
Product Description : VersaKrimp Temp-Term Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 10 (M5), Carton
Series Number : 19203
Status : Active
Product Category : Ring and Spade Terminals
Engineering Part Number : C-T-328-10



Documents and Resources

Drawings

192030099_sd.pdf

Specifications

PS-19902-013-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Downloaded from Arrow.com.

- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19203
Description	VersaKrimp Temp-Term Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 10 (M5), Carton
Comments	650° F (343° C)
Keyword	Ring Terminal, Ring Terminals
Product Name	VersaKrimp
Style	Ring, High Temperature
Type	High Temperature Terminal
UPC	800755059519

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Plating Mating	Nickel
Net Weight	1.480/g
Packaging Type	Carton
Stud Size	10 (M5)
Wire Size (AWG)	10, 12
Wire Size mm^2	4.00-6.00

Downloaded from Arrow.com.

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 22-10 AWG and 6.0mm² - 0.5mm²	640030100
ServiceGrade Hand Crimp Tool - Ratchet	640160038

Downloaded from Arrow.com.