



Dieless Mechanical Crimper, Heavy Duty Forged Steel, #8 Str - 2/0 Str. Copper aircraft cable (flexible)

By Burndy
Catalog # [MY286](#)

Dieless Mech #8Str-2/0Str CU Aircraft Fx

Features

- Two-ply covered handles of MY29-3C and MY29-11C designs
- Heavy duty forged steel back body and handles
- Strong reinforced forged steel back
- Setting plate
- .31" diameter hole for bench mounting operations
- Comfort grips
- Extra strong heavy duty reinforced handles
- Indentor die
- Knurled steel adjusting knob

Application

Crimping

Specifications

Standards - RoHS Compliance EX
Status

Conductor

Crimping Ranges #8 Str. - 2/0 Str.

Dimensions

Length 22.65 in



Width 4.86 in
Weight 8 lb.
Height 1.12 in
Dimensions 22.65 in x 4.86 in x 1.12 in

General

Trade Name HYTOOL™
Application - For Use On #8-2/0 AWG Copper Aircraft Cable Flex (YAE-L, YAEV-RS, YAEV-H, YAV-RH)

Type Crimper
UPC 12 Digit 781810461976
UPC 14 Digit GTIN 00781810461976
Finish Type Black Matte
Tool Type Mechanical Dieless Crimper
UPC 781810461976
Die Type Dieless

Logistics

Package Contents Tool only
Minimum Pack Quantity 1

Product Assets

[Catalog \[English\]](#)