

Aptiv Connection Systems Catalog

Customer Service

Samples Request

Find by Feature

Browse by Category

Browse by Application

Comparison List (0)

Share

Search

Enter part number or keyword

Search Results (1)

Search Options

1 Result(s): [All] - 10774281

☐ Compare

60012431 - HPCS 2.8 Female Sealed Tin Plating Terminal Assembly, Cable Range 0.50 - 1.00 mm2

☐ Compare

HPCS 2.8 Female Sealed Tin Plating Terminal Assembly, Cable Range 0.50 - 1.00 mm2



Part # 60012431

[Question about this product?](#)

Attributes

Documents (1)

Part # :	60012431
Description :	HPCS 2.8 Female Sealed Tin Plating Terminal Assembly, Cable Range 0.50 - 1.00 mm2
Product Type :	Terminal
Status :	✓ Active
Blade size [mm] :	2.8
Series :	2.8
Gender :	Female
Sealable :	Sealed
Material :	CuCrSiTi/CrNi
Weight [g] :	0
Plating :	Tin
Minimum Cable Diameter [mm] :	1.40
Maximum Cable Diameter [mm] :	2.10
Minimum Cable Core Cross Section [mm2] :	0.50
Maximum Cable Core Cross Section [mm2] :	1.00
Remarks :	Former FCI Product, Delphi PN:10774281, High Performance version, Long auxiliary steel spring in CrNi, High resistance against fretting corrosion and vibration, Suitable for secondary lock

Certain products listed on this website may be subject to restricted usage or distribution or may not be available. For additional information, please contact your local sales office.