

Han 10B HTE M25 PFT CL



Image is for illustration purposes only. Please refer to product description.

Part number	19 30 010 1141
Specification	Han 10B HTE M25 PFT CL
HARTING eCatalogue	https://b2b.harting.com/19300101141

Identification

Category	Hoods/Housings
Series of hoods/housings	Han [®] B
Type of hood/housing	Panel feed through housing
Type	High construction

Version

Size	10 B
Version	Top entry
Cable entry	1x M25
Locking type	Central locking lever (on the hood)
Field of application	Standard hoods/housings for industrial connectors

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (seal)	NBR
RoHS	compliant
ELV status	compliant



Pushing Performance

Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Specifications and approvals

CE	Yes
----	-----

Commercial data

Packaging size	1
Net weight	293.84 g
Country of origin	China
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors