

Stainless Steel W Die, Index BG

By Burndy
Catalog # [WBG](#)

W Die, Index BG



Features

- Durable Stainless Steel Material
- Circumferential Crimp
- Twin W-RT Style
- Die Index BG

Application

Crimping

General

Application - For Use On	Use with MD6, MD7 Mechanical, Y500CTHS Hydraulic, PAT600 and PATMD Battery Actuated Crimpers
Catalog Number	WBG
Construction Material - Main	Stainless Steel
Crimp Force Capacity	6 ton
Die Index	BG
Die Type	W Die
EU RoHS Indicator	Yes
Sub Brand	W-DIE
Type	W-Die for Hydraulic Crimping Tools
UPC	781810440056
UPC 14 Digit GTIN	00781810440056

Conductor Related

Crimping Ranges	Copper: #6 AWG - 4/0 AWG; Aluminum: #6 AWG - 1/0 AWG; ACSR: #6 AWG - 1/0 AWG
-----------------	--

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Standards - RoHS Compliance	EX
Status	

Logistics

Carton Quantity	120
Minimum Pack Quantity	1
Package Contents	Die only
Pallet Quantity	11520

Product Assets

- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_WDIE_Lineart](#)
- [Sales Drawings - 30000157](#)
- [Specifications - WBG](#)