



**Part Number :** [397000703](#)  
**Product Description :** 3.50mm Pitch, Eurostyle  
Fixed-Mount Push-Button Terminal Block, 45°  
Modular, 5A, 20-16 AWG, Light Gray, 3 Circuits  
**Series Number :** 39700  
**Status :** Active  
**Product Category :** Terminal Blocks and  
Barrier Strip  
**Engineering Number :** M710-02-03-9



---


## Documents & Resources

**Drawings**  
[397000703\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

## Part Details

### General

Status	Active
Category	Terminal Blocks and Barrier Strip
Series	39700
Description	3.50mm Pitch, Eurostyle Fixed-Mount Push-Button Terminal Block, 45° Modular, 5A, 20-16 AWG, Light Gray, 3 Circuits
Application	Wire-to-Board
Component Type	One Piece
Product Family	Terminal Blocks & Barrier Strips
Product Name	Eurostyle Fixed Mount
Type	PCB Terminal Blocks and Connectors
UPC	78172542533

### Electrical

Current - Maximum per Contact	5.0A
Voltage - Maximum	300V

### Physical

Circuits (Loaded)	3
Circuits (maximum)	3
Color - Resin	Gray (Light)
Entry Angle	45° Angle
Lock to Mating Part	No
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	1.600/g
Number of Rows	1
Orientation	45° Angle
Panel Mount	Yes

Pitch - Mating Interface	3.50mm
Polarized to Mating Part	No
Stackable	No
Temperature Range - Operating	-40° to +105°C
Wire Size (AWG)	16, 18, 20

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

---

---

This document was generated on Nov 09, 2024