

Product data sheet

Specifications



APC PDU 3-POLE 20AMP, BOLT ON, SQUARE D BREAKER

PD3P20ABBSD

Overview

Lead time	Usually Ships within 2 Weeks
-----------	------------------------------

Main

Number of cables	1
------------------	---

Physical

Colour	Black
Height	7.62 cm
Width	7.62 cm
Depth	7.62 cm
Product weight	0.46 kg
Mounting mode	Not rack-mountable

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	0...45 °C
Storage Relative Humidity	0...95 %
Storage altitude	0.00...15240.00 m

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.16 cm
Package 1 Width	10.16 cm
Package 1 Length	10.16 cm
Package 1 Weight	0.5 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Offer Sustainability

EU RoHS Directive

Under investigation

Recommended replacement(s)