

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1212040001

Status:

Active

Overview:

mPm® DIN Valve Connectors

Description:

mPm® DIN Valve Connector, Form C, External Thread, 2 Pole Plus Ground Terminal, 250V AC/300V DC, Black Nitrile Gasket



Documents:

Drawing (PDF)

Product Specification PS-121201-001-001 (PDF)

Packaging Specification PK-121204-C25-001 (PDF)

Test Summary STR-1299-001 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Field Attachable / Accessories
Series	121204
Form	C
IP Rating	IP65, IP67
Material - Contact	Brass
Overview	mPm® DIN Valve Connectors
Product Name	mPm®
Type	Field Attachable Connector
UPC	884982238992
Physical	
Cable Diameter	N/A
Coupling Type	External Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	N/A
Keyway	None
Material - Connector Body	Polyamide
Material - Coupling Nut	N/A
Material - Plating Mating	Silver
Net Weight	10.715/g
Orientation	90° Angle
Pitch - Mating Interface	8.00mm
Poles	2
Temperature Range - Operating	-40°C to +90°C
Wire Size AWG	N/A
Electrical	
Current - Maximum per Contact	16.0A
Voltage - Maximum	250V AC / 300V DC
Material Info	
Engineering Number	C25200N0T
Reference - Drawing Numbers	
Packaging Specification	PK-121204-C25-001
Product Specification	PS-121201-001-001
Sales Drawing	SD-121204-001
Test Summary	STR-1299-001

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Contained Per -ED/01/2017 (12 January 2017)

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

121204 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION