

CUC-V14-A1RBK-PC - Panel mounting frames



1413985

<https://www.phoenixcontact.com/us/products/1413985>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Panel mounting frames, degree of protection: IP65



Commercial data

Item number	1413985
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB17
Product key	ABNODZ
Catalog page	Page 360 (C-2-2019)
GTIN	4055626082325
Weight per piece (including packing)	11 g
Weight per piece (excluding packing)	11 g
Customs tariff number	85389099
Country of origin	DE

CUC-V14-A1RBK-PC - Panel mounting frames



1413985

<https://www.phoenixcontact.com/us/products/1413985>

Technical data

Product properties

Product type	Panel mounting frame
Type	Version 14

Insulation characteristics

Degree of pollution	2
---------------------	---

Dimensions

Width	24.1 mm
Height	55.3 mm
Length	33.2 mm

Material specifications

Material	PA 6
Flammability rating according to UL 94	V0
Seal material	NBR
	HNBR

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-5 °C ... 55 °C

CUC-V14-A1RBK-PC - Panel mounting frames



1413985

<https://www.phoenixcontact.com/us/products/1413985>

Classifications

ECLASS

ECLASS-11.0	27440210
ECLASS-12.0	27440210
ECLASS-13.0	27440210

ETIM

ETIM 8.0	EC002310
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

CUC-V14-A1RBK-PC - Panel mounting frames



1413985

<https://www.phoenixcontact.com/us/products/1413985>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

CUC-V14-A1RBK-PC - Panel mounting frames

1413985

<https://www.phoenixcontact.com/us/products/1413985>



Accessories

FOC-V14-F1ZNI-EM/SJO - Panel mounting frames

1413981

<https://www.phoenixcontact.com/us/products/1413981>



RJ45 panel mounting frame for transceiver, IP67, for push-pull interlocking, metal, for square mounting cutout, with seal and mounting screws

CUC-V14-F1ZNI-EM/R4F8 - Panel mounting frames

1413961

<https://www.phoenixcontact.com/us/products/1413961>



RJ45 panel mounting frame, IP67, for push-pull interlocking, metal, for rectangular mounting cutout, with seal and mounting screws, incl. RJ45 insert with IDC cable connection

CUC-V14-A1RBK-PC - Panel mounting frames

1413985

<https://www.phoenixcontact.com/us/products/1413985>



CUC-V14-F1ZNI-EM/R4B8 - Panel mounting frames

1413962

<https://www.phoenixcontact.com/us/products/1413962>



RJ45 panel mounting frame, IP67, for push-pull interlocking, metal, for rectangular mounting cutout, with seal and mounting screws, incl. RJ45 coupling module

CUC-V14-F1ZNI-EM/R4O - Panel mounting frames

1413963

<https://www.phoenixcontact.com/us/products/1413963>



RJ45 panel mounting frame, IP67, for push-pull interlocking, metal, for PCB connection, for square panel cutout, with grommet and mounting screws

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com