# Specifications



## Eaton TTM560

Eaton Bussmann series low voltage british standard fuse, 560A, AC 660 V, DC 450 V, V88/C2, 74 x 210 mm, gL/gG

| General specifications | |
|---|---|
| **PRODUCT NAME** | Eaton Bussmann series low voltage british standard fuse |
| **CATALOG NUMBER** | TTM560 |
| **MODEL CODE** | 560A 660V AC / 450V DC BS88 FUSE |
| **EAN** | 5996516026700 |
| **PRODUCT LENGTH/DEPTH** | 210 mm |
| **PRODUCT HEIGHT** | 75 mm |
| **PRODUCT WIDTH** | 75 mm |
| **PRODUCT WEIGHT** | 1080 g |
| **COMPLIANCES** | CE Marked<br>RoHS Compliant |
| **CERTIFICATIONS** | BS88<br>IEC 60269<br>EAC |
| **PRODUCT TYPE** | Low voltage british standard fuse |

Powering Business Worldwide

Downloaded from Arrow.com.

## Resources

| | |
|---|---|
| CATALOGS | eaton-bussmann-series-low-voltage-fuses-catalog-ca134002en-en-us.pdf |
| DECLARATIONS OF CONFORMITY | eaton-low-voltage-british-standard-fuse-declaration-of-conformity-uk250884en.pdf<br><br>eaton-low-voltage-british-standard-fuse-declaration-of-conformity-eu250006en.pdf |
| MCAD MODEL | eaton-iec-lv-fuses-mcad-3d-models-ttm-450-670a.stp |
| MULTIMEDIA | Eaton Bussmann - Red Spot fuse links |
| TECHNICAL DATA SHEETS | 10078 Red spot centre bolted fuses:TB, TBC, TC, TF, TKF, TKM, TMF, TM, TMT, TTM, TLM, TT, TLU,TXU fuses |

| | |
|---|---|
| **PROJECT NAME:** | |
| **PROJECT NUMBER:** | |
| **PREPARED BY:** | |
| **DATE:** | |

**Eaton Corporation plc** Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

Downloaded from Arrow.com.