


Specifications			Notes	Revision History					
Description	Value	Unit		Version	Description			Date	Approved
Technology	Electro-Mechanical		1) All dimensions are in mm unless otherwise noted 2) All parts meet RoHS	1	Released from Engineering			10/21/2013	J.S
Resonant Frequency	2,048	(Hz)							
Rated Voltage	1.5	(V)							
SPL @ 10cm	85	(dBA)							
Coil Resistance	6.5	(ohm)							
Mount Type	Thru-hole								
Voltage Range	1 ~ 3	(V)							
Max Rated Current	80	(mA)							
Housing Material	NORYL								
Operating Temperature	-20 ~ +60	°C							
Storage Temperature	-20 ~ +60	°C	 DB UNLIMITED	Drawn by	Date	Checked by	Date	Approved by	Date
Weight	2	(g)		A.B.	10/21/2013	C.E.	10/21/2013	J.S	10/21/2013
Electro-Mechanical Transducer				TE122001-3					

Additional considerations can be found at www.dbunlimitedco.com/technical-articles.