

Representative Image

Catalog No. TY300-50X

Description: CABLE TIE 50LB 12IN UV BLACK NYLON

UPC No 5414363064169

Home > Wire & Cable Management > Ty-Rap > Cable ties

"Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius, Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, UL/IEC 62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 304mm, Width of 4.8mm, Thickness of 1.24mm , Tensile Strength Rating of 220 Newtons, 1000 Pack"

Descriptors

Category	Cable ties
Special Features	The integrally formed polyamide pawl combines low insertion and high locking strength. The low profile head significantly reduces the potential for snagging during installation. Quick and easy pull through increases productivity, reduces operator fatigue. Tail with finger grip design that helps operator grasp and pull ties snugly. Sure grip tab keeps the tail from popping out while being treated, then holds it it securely for final tightening by hand or tool

Specifications

Material	Nylon/Polyamide 6.6
Color	Natural
Lock Mechanism	Plastic Pawl
Tensile Strength	222 newtons , 50 pounds

Classifications

Brand Name	Catamount
Standard	UL E49405

Dimensions

Width	4.8mm , 0.189 in
Length	430 mm , 16.929 in
Thickness	1.3 mm , 0.051 in
Bundle Diameter	3 to 122.5 mm , 0.118 to 4.823 in

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 240 Compliant
TSCA	TSCA Section 6(h) Compliant
POPs	POPs 28 Compliant

Downloaded from Arrow.com.

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
CSA	2884	441406	N/A	70037393_2015-07-18	N/A
UL	E49405	N/A	ZODZ	N/A	N/A

Downloaded from Arrow.com.