



HummingBoard Pulse i.MX8M Mini



Quad 1.8GHz i.MX8M Mini
2GB RAM | 8GB eMMC
0° to 70° C | Lightspeur 2803 AI Accelerator
Inc. Heatsink

SKU: SRMM8QDW0GD02GE008U00CH

HummingBoard Pulse – Quad 1.8GHz i.MX8M Mini

- NXP i.MX8M Mini ARM A53
- Gyrfalcon Technology Lightspeur® 2803 AI Accelerator
- 2GB RAM
- 8GB eMMC
- Commercial Temp. (0° to 70° C)
- Size: 102mm x 69mm

For more information visit **HummingBoard Pulse**.

***Please note:** this product does not include any accessories or power adapter. Please select a power adapter at the bottom of the cart page before you finalize your purchase. Also, you can find all accessories here.

Weight	0.45 kg
CPU Name	NXP i.MX8M Mini
CPU Type	4 x Arm Cortex A53 + M4
CPU Clock Speed	1.8GHz
Memory	2GB
Storage	8GB eMMC
Wireless Connectivity	None
Connectivity	Ethernet, HDMI, MIPI-CSI, MIPI-DSI, PCIe, PoE, UART, USB 2.0, USB OTG
Temperature	0° to 70° C
OS Support	Linux



<https://shop.solid-run.com/product/SRMM8QDW0GD02GE008U00CH//11-22-19>