Part Number : 135140001
Product Description : Button RFID Tag, 30.0mm Read Range, 30.00mm Diameter Footprint, For Metal Surfaces, Screw or Adhesive Attachment
Series Number : 13514
Status : Active
Product Category : Asset Tracking



Documents and Resources

Drawings

135140001_sd.pdf

Specifications

135140001-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Reviewed
China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Downloaded from Arrow.com.

Additional Product Compliance Information

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Asset Tracking
Series	13514
Description	Button RFID Tag, 30.0mm Read Range, 30.00mm Diameter Footprint, For Metal Surfaces, Screw or Adhesive Attachment
Component Type	RFID Tag
Product Name	RFID Solutions
Type	For Metal Surfaces
UPC	196823154126

Electrical

Frequency	13.56 MHz

Physical

Dimensions	30.00mm dia x 3.00mm Thickness
Mounting Style	Adhesive, Screws
Net Weight	3.700/g
Outer Diameter	30.00mm
Packaging Type	Bag
Read Range	30.0mm
Thickness	3.00mm

Downloaded from Arrow.com.