HSB63

General purpose, flexible heat shrink tubing for the protection, insulation and bundling of cables.

Catalog Number:	**HSB63**
EAN Number:	05414363104452
UPC Number:	78621053851
Description:	PLG thin wall flexible heat shrink tubing, with expanded diameter 1.6 mm, black, shrink ratio 2:1, length 12 m

Technical Information	
Tubing Family	PLG
Wall Thickness	thin
Shrink Ratio	2:1
Tube Characteristics	single wall
Material	PE crosslinked polyolefin
Temperature Range	-55°C to +125°C
Shrink Temperature	> +110°C
IP Rating	IP60
Flammability Rating	self-extinguishing
Colour	black
Silicone free	yes
Lead/Cadmium free	yes
Dielectric Strength	20 KV/mm
Chemical Resistance	good
Ordering Information	
Expanded Diameter as Supplied (inch)	1/16
Expanded Diameter as Supplied (mm)	1.6
Fully Recovered Diameter (mm)	0.8
Wall Thickness before Shrinking (mm)	0.2
Wall Thickness after Shrinking (mm)	0.4
Length (m)	12
Packaging Type	Dispenser box

Downloaded from Arrow.com.