
**Part Number :** 982660237
**Product Description :** 0.50mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 152.00mm Cable Length, Tin (Sn) Plating, 22 Circuits
**Series Number :** 98266
**Status :** Active
**Product Category :** Flat-Flexible Cable (FFC)



## Documents and Resources

### Drawings

982660237_sd.pdf

STEP AP242

SOLIDWORKS

Creo

### Specifications

PS-98266-001-001.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| China RoHS | Not Reviewed |
| EU ELV | Not Reviewed |
| Low-Halogen Status | Not Reviewed |
| REACH SVHC | Not Reviewed |
| EU RoHS | Not Reviewed |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Downloaded from Arrow.com.

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Flat-Flexible Cable (FFC) |
| Series | 98266 |
| Description | 0.50mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 152.00mm Cable Length, Tin (Sn) Plating, 22 Circuits |
| Comments | Contacts on the same side, Type A |
| Product Name | Premo-Flex FFC Jumper |
| UPC | 756054771846 |

### Electrical

| | |
|---|---|
| Current - Maximum per Contact | 0.5A |
| Voltage - Maximum | 60V AC |

### Physical

| | |
|---|---|
| Cable Length | 152.00mm |
| Circuits (Loaded) | 22 |
| Contact Layout Type | A (same side) |
| Design Feature | Extra-Flexible |
| Material - Plating Mating | Tin |
| Net Weight | 1.089/g |
| Packaging Type | Bag |
| Pitch - Mating Interface | 0.50mm |
| Temperature Range - Operating | -40° to +105°C |
| Termination Style | FFC Connector |
| Wire/Cable Type | Flat Flex Cable |

Downloaded from Arrow.com.

| | |
|---|---|
| Wire Size (AWG) | N/A |

## Mates With / Use With

### Mates with Part(s)

| Description | Part Number |
|---|---|
| Easy-On FFC/FPC Connector, 0.50mm Pitch, V-Flip Series, Vertical, 4.05mm Height, 22 Circuits, Copper Alloy, Tin-Bismuth Plating | 5019512200 |
| Easy-On FFC/FPC Connector, 0.50mm Pitch, Slider Series, Right-Angle, Top Contact, 2.00mm Height, 22 Circuits, Tin-Bismuth Plating | 524352272 |
| Easy-On FFC/FPC Connector, 0.50mm Pitch, Slider Series, Right-Angle, Bottom Contact, 2.00mm Height, 22 Circuits, Tin-Bismuth Plating | 524372272 |
| Easy-On FFC/FPC Connector, 0.50mm Pitch, Slider Series, Vertical, 3.90mm Height, 22 Circuits, Tin-Bismuth Plating | 525592270 |
| Easy-On FFC/FPC Connector, 0.50mm Pitch, Surface Mount, Vertical, Non-ZIF, Standard Footprint, Tin Bismuth Plating, Short Terminal Type, Black, 22 Circuits | 781192210 |
| Easy-On FFC/FPC Connector, 0.50mm Pitch, Surface Mount, Vertical, Non-ZIF, Reverse Footprint, Tin Bismuth Plating, Long Terminal Type, Black, 22 Circuits | 781272210 |



Downloaded from Arrow.com.