Part Number : 1301470154
Product Description : Watertite Extreme Receptacle with Locking Blade, Single Flip Coverplate, 4 Pole/5 Wire, NEMA L23-20, 3ø 600V
Series Number : 130147
Status : Active
Product Category : Wiring Devices
Engineering Part Number : 67W83



Documents and Resources

Drawings

1301470154_sd.pdf

3D Models and Design Files

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Downloaded from Arrow.com.

Part Details

General

Status	Active
Category	Wiring Devices
Series	130147
Description	Watertite Extreme Receptacle with Locking Blade, Single Flip Coverplate, 4 Pole/5 Wire, NEMA L23-20, 3ø 600V
IP Rating	IP67
NEMA Configuration	NEMA L23-20
Product Name	Watertite Extreme
Specialty	N/A
Type	Receptacle
UPC	78678871569

Agency

UL	E68122

Electrical

Current - Maximum per Contact	20.0A
GFCI	No
Voltage - Maximum	3Ø 600V

Physical

Cord Type	N/A
Flange	No
Flip Lid	Yes
Gender	Female
Length	N/A
Lighted Connector	No
Locking Blade	Yes
Poles	4-pole/5-wire
Receptacle Type	Single

Downloaded from Arrow.com.

Downloaded from Arrow.com.