

 Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



Quick Links

[Check Pricing & Availability](#)
[Search for Tooling](#)
[Product Feature Selector](#)
[Contact Us About This Product](#)

 Active

? Header Type = Receptacle
 ? PCB Mount Style = Surface Mount
 ? Right Angle Mount Angle
 ? Number of Rows = Dual
 ? Number of Positions = 12

[View all Features](#) | [Find Similar Products](#)

Product Drawings:

Catalog Pages/Data Sheets:

? None Available

Product Specifications:

[AMP 1.25mm F -P Connector \(Board To Board\)](#) (PDF, Japanese)

Application Specifications:

? None Available

Instruction Sheets:

? None Available

CAD Files: ([CAD Format & Compression Information](#))

- ? 2D Drawing (DXF, Version G)
- ? 3D Model (IGES, Version G)
- ? 3D Model (STEP, Version G)

Additional Information:

? Product Line Information

Additional Product Images:

? PCB Layout

Related Products:

? Tooling

List all Documents

Product Type Features:

? PCB Mount Style = Surface Mount

? Mount Angle = Right Angle

? Number of Positions = 12

? PCB Retention Feature = Yes

? Polarization = With

? Product Type = Header

Body Related Features:

? Header Type = Receptacle
 ? Number of Rows = Dual
 ? PCB Retention Method = Hold Down Post
 ? Polarization Method = Long Rib
 ? Centerline (mm [in]) = 1.25 [0.049]

Contact Related Features:

? Contact Mating Area Plating = Pre -Tin
 ? Contact Material = Phosphor Bronze

Housing Related Features:

? Housing Material = PPS Resin
 ? Housing Color = Black
 ? Housing Flammability Rating = UL 94V -0

Industry Standards:

- ? RoHS/ELV Compliance = RoHS compliant, ELV compliant
- ? Lead Free Solder Processes = Reflow solder capable to 245°C
- ? RoHS/ELV Compliance History = Converted to comply with RoHS directive

Packaging Related Features:

? Packaging Method = Reel

? Packaging Quantity = 1,500

Other:

? Brand = AMP