



ITEM NO.	DESCRIPTION	QTY.
1	HOUSING	1
2	MAGNET	2
3	POGO PIN	4

REVISIONS			
REV.	DESCRIPTION	DATE	BY
1	ORIGINAL	DRAWN DATE	










SPECIFICATIONS

CURRENT RATING:	3A
VOLTAGE RATING:	12V
WITHSTANDING VOLTAGE:	500V
INSULATION RESISTANCE:	1000MΩ MIN FOR 1 MIN
CONTACT RESISTANCE:	50mΩ MAX
TEMPERATURE RANGE:	-25°C TO 80°C
INSULATOR MATERIAL:	HTN
INSULATOR COLOR:	BLACK
CONTACT MATERIAL:	BRASS
CONTACT PLATING:	5µ" GOLD PLATING
MAGNET MATERIAL:	N52
MATING CYCLES:	10000
MATING PARTS:	MPM-VA0-104-2R02-A00 MCM-YA0-104-2R02-BK0



RECOMMENDED PCB LAYOUT
TOLERANCE ±0.05

NOTE:IR REFLOW AND WAVE SOLDERING NOT RECOMMENDED AS THE PROCESSES CAN DEMAGNETIZE THE CONNECTOR MAGNETS.

EDAC

RoHS COMPLIANT

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC, AND SHALL NOT BE REPRODUCED , OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN BY	V.K.	FEMALE CONNECTOR, RECTANGULAR, 2.2MM PITCH, 4 POSITIONS	
DRAWN DATE	08/06/2025		
CHECKED BY	R.S.M.		
CHECK DATE	08/06/2025	PART NUMBER	MPF-VA0-104-2P02-A00
TOLERANCES		MATERIAL	SIZE A
.X	±0.3		REVISION
.XX	±0.2	ALL DIMENSIONS AND TOLERANCES IN MM	1
.XXX	±0.1	SCALE 3:1	SHEET 1 OF 1

Downloaded from Arrow.com.