





Notes:

- *  Important Dimension To Check.
- * Waterproof Rate: IP68(mating).
1M Depth Of Water In 24 Hours.
- * Housing: Thermoplastic, UL94V-0,
Natural White.
- * Gasket: Silicone, Gray.
- * Seals: Silicone, Gray
- * Current Rating: 5A maximum.
- * 適用電子線20AWG~22AWG
- * Voltage Rating:250V DC/AV maximum.
- * Operating Temperature: -40~+105℃

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Packing



- QUANTITY
- 1. 2500Set Per Carton
 - 2. Net Weight: 2.3Kg/Carton.
 - 3. Gross Weight: 3.0Kg/Carton.

UNIT:mm		TITLE		Amphenol LTW		ITEM NO		DRAWN BY		DATE	
TOLERANCE ±0.5mm		SSL1.2 2P M CONN. ASS'Y		安費諾亮泰企業股份有限公司		SSL12-P2FP0-M00001		Cary		2014-07-31	
SCALE 2:1		SIZE A4		SHEET 2 OF 2		DWG NO		CHECKED BY		DATE	
REV. A		WC-REV. A.1		QC: Inspection item		SSL12-P2FP0-M00001		Fisher		2014-07-31	
						CUSTOMER		APPROVED BY		DATE	
						ALTW		Jerry		2014-07-31	