


Part Number : [349610385](#)

Product Description : Mini50 Unsealed Right-Angle Header, UL 94 HB, 3 Rows, 38 Circuits, Polarization Option C, Dark Gray, Tray

Series Number : 34961

Status : Obsolete

Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

[349610385_sd.pdf](#)

[PK-31302-070-001.pdf](#)

Specifications


[349590001-AS-CH-000.pdf](#)

[PS-34959-001-001.pdf](#)

[TS-34961-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Duty-To-Declare
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	PCB Headers and Receptacles
Series	34961
Description	Mini50 Unsealed Right-Angle Header, UL 94 HB, 3 Rows, 38 Circuits, Polarization Option C, Dark Gray, Tray
Application	Automotive, Wire-to-Board
Comments	38 x 0.50mm blades = 4.0A
Component Type	PCB Header
Product Name	Mini50
UPC	191128819787

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	500V DC

Physical

Breakaway	No
Circuits (Loaded)	38
Circuits (maximum)	38
Color - Resin	Gray (Dark)
Durability (mating cycles max)	10
First Mate / Last Break	No
Glow-Wire Capable	No

Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	SPS
Net Weight	6.400/g
Number of Rows	3
Orientation	Right Angle
Packaging Type	Tray
PCB Locator	Yes
PCB Retention	No
PC Tail Length	2.75mm
Pitch - Mating Interface	2.00mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Stackable	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Through Hole

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mini50 Unsealed Receptacle, UL 94 HB, 3 Rows, with CPA, 38 Circuits, Polarization Option C, Dark Gray	<u>349590385</u>
Mini50 Unsealed Receptacle, UL 94 HB, 3 Rows, without CPA, 38 Circuits, Polarization Option C, Dark Gray	<u>349590392</u>

This document was generated on May 27, 2026