
HellermannTyton

Technical data sheet

Article number:
170-01108 Twist-In-FR 38



Product Group	Self-closing, flame-retardent polyester sleeving
Product Family	Helagaine Twist-In-FR
Material	Polyester (PET)
Colour	Black with White Identification Yarn (BKIDWH)

Application Method	For optimum cable protection including flexibility, we recommend that a filling level of 75% is not exceeded.
Application Range	Indoor Use
Bundle Ø max.	38 mm
Bundle Ø min.	32 mm
Melting Point	+240 °C
Operating Temperature	-50 °C to +125 °C
Package Content	15 m
Package Content packed in	reel
Specifications	ECE R-118-03 Abschnitt 8 / Annex 8, EN 45545-2
UL-File Number	E197993

HF RoHS

EN 45545-2 ECE R-118

created on 4. September 2026, 9:40 am

Technical changes and errors reserved. It´s up to the customer to check the suitability for a specific application by means of tests.

Downloaded from Arrow.com.