



Part Number : [191600044](#)
Product Description : Wing Lock Splice for 18-10
AWG Wire, Yellow
Series Number : 19160
Status : Active
Product Category : Splices
Engineering Number : WL-Y

Documents & Resources

Drawings


[191600044 sd.pdf](#)

Specifications

[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)



Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Splices
Series	19160
Description	Wing Lock Splice for 18-10 AWG Wire, Yellow
Product Name	Wing Lock
Type	Wing Lock
UPC	800753110489

Agency

CSA	LR18689
UL	E32244

Electrical

Voltage - Maximum	600V
-------------------	------

Physical

Barrel Type	Closed
Color - Resin	Yellow
Flammability	94V-2
Insulation	Nylon (PA)
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.830/g
Packaging Type	Bag
Temperature Range - Operating	105°C
Wire Insulation Diameter	9.91mm max.

Wire Size (AWG)	10, 12, 14, 16, 18
-----------------	--------------------

This document was generated on Sep 22, 2025