



Part Number : [190740024](#)

Product Description : Krimptite Steel Star Ring Tongue Terminal for 14-16 AWG Wire, Stud Size 8 (M4), Mylar Tape Carrier

Series Number : 19074

Status : Active

Product Category : Ring and Spade Terminals

Engineering Number : SRB-S-129-08T

Documents & Resources

Drawings

[Drawing 190740024_sd.pdf](#)

3D Models and Design Files


[3D Model 190740024_stp.zip](#)

Specifications

[Product Specification PS-19902-011-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19074
Description	Krimptite Steel Star Ring Tongue Terminal for 14-16 AWG Wire, Stud Size 8 (M4), Mylar Tape Carrier
Keyword	Ring Terminal, Ring Terminals
Product Family	Solderless Terminals
Product Name	Krimptite
Type	Ring
UPC	800753079106

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed
Insulation	None
Material - Plating Mating	Tin
Net Weight	0.540/g
Packaging Type	Adhesive Tape on Reel
Stud Size	8 (M4)
Termination Interface Style	Crimp or Compression
Wire Size (AWG)	14, 16

Application Tooling

Global

Description	Part Number
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	<u>190270184</u>

This document was generated on Jul 28, 2024