

BIT E6,3 0,6X3,5X70**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

1/4" hexagon drive to DIN 3126, form E6.3 for direct machine connection

Slot-head bits DIN 5264, 1/4" drive, E6.3 DIN 3126

General ordering data

Version	Accessories, Screwdriver insert
Order No.	9024020000
Type	BIT E6,3 0,6X3,5X70
GTIN (EAN)	4008190852627
Qty.	5 pc(s).
Delivery status	Discontinued
Available until	2021-01-31
Alternative product	2748920000

Creation date May 22, 2025 11:58:11 PM CEST

Catalogue status 10.05.2025 / We reserve the right to make technical changes.

BIT E6,3 0,6X3,5X70**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Width	70 mm	Width (inches)	2.756 inch
Net weight	9.4 g		

Technical data

Description of article	Bit with slotted blade, 0.6 x 3.5 x 70
------------------------	---

Electric screwdriver

Weight	9.6 g
--------	-------

Screwing tools

Blade length	70 mm	Blade thickness (A)	0.6 mm
Blade width (B)	3.5 mm	Form	E 6.3 DIN 3126, Slotted

Classifications

ETIM 6.0	EC002116	ETIM 7.0	EC002116
ETIM 8.0	EC003864	ETIM 9.0	EC003864
ETIM 10.0	EC003864	ECLASS 9.1	21-04-04-90
ECLASS 10.0	21-04-04-90	ECLASS 11.0	21-04-42-04
ECLASS 12.0	21-04-42-04	ECLASS 13.0	21-04-42-04
ECLASS 14.0	21-04-42-04	ECLASS 15.0	21-04-42-04

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
Brochures	