



REV	
A	DTHD04-1-12P

REVISIONS			
SYM	DESCRIPTION	DATE	APPROVED
NC	NEW RELEASE PER E.O. A14636	12-6-94	R.D.R.
A	REVISED PER E.O. P18603	6-29-04	ADR









6 DATE CODE: MONTH IS REPRESENTED BY SEQUENTIAL ALPHA CHARACTERS. EX: A = JANUARY.
YEAR IS REPRESENTED BY LAST NUMERIC DIGIT. EX: 2 = 2002.

5 MATERIAL: HOUSING: PLASTIC, GROMMET: RUBBER.

4 THIS RECEPTACLE MATES WITH DTHD06-1-12S-**** PLUG.
(**** = ALL MODIFICATIONS)

3 FOR CONTACT AND WIRE PERFORMANCE AND APLICATION CHARACTERISTIC SEE ENVELOPE DRAWING 0425-015-0000.

2 DIMENSION TOLERANCE: ±.025 [.64].

1 DIMENCIONS ARE IN INCHES [mm].

NOTES: UNLESS OTHERWISE SPECIFIED.

WIRE INSULATION DIA			
CONTACT SIZE	MINIMUM O.D.	MAXIMUM O.D.	WIRE RANGE [mm^2] REF. ONLY 4
12	.134 [3.40]	.170 [4.32]	12-14 AWG [3.0-2.0]

	SIGNATURE & DATE
DR	V. TOMSA DEC-30-02
CHK	
PE	Vladimir Tomsa JUN-10-04
APP'D	D Meyer 6/21/04
SCALE	3:1 WT

RECEPTACLE
#12 HD CONTACT
DTHD SERIES
COLOR: BLACK

ENVELOPE

CP — MATL. CODE

The Deutsch Company
DEUTSCH I.P.D.
3850 INDUSTRIAL AVE.
HEMET, CALIF. 92545

B — DWG SIZE — DTHD04-1-12P

CODE 11139 — SHEET 1 OF 1

Downloaded from Arrow.com