



Part Number : [2064620500](#)
Product Description : Micro-Fit+ Terminal
Position Assurance (TPA) Retainer, 5 Circuits,
3.00mm Pitch, UL 94V-0, Glow-Wire Capable,
Natural
Series Number : 206462
Status : Active
Product Category : Connector Accessories



Documents & Resources

Drawings

[2064620500_sd.pdf](#)
[2064620000-PK-000.pdf](#)

3D Models and Design Files

[2064620500_stp.zip](#)

Specifications

[2064600001-AS-000.pdf](#)
[2064600000-PS-000.pdf](#)
[2159530000-PS-000.pdf](#)
[2064600000-TS-000.pdf](#)
[2064600001-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC

- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Connector Accessories
Series	206462
Description	Micro-Fit+ Terminal Position Assurance (TPA) Retainer, 5 Circuits, 3.00mm Pitch, UL 94V-0, Glow-Wire Capable, Natural
Component Type	Terminal Position Assurance
Product Name	Micro-Fit+
UPC	191130008704

Agency

UL	E29179
----	--------

Physical

Circuits (Loaded)	5
Circuits (maximum)	5
Color - Resin	Natural
Flammability	94V-0
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.114/g
Number of Rows	1
Packaging Type	Bag
Temperature Range - Operating	-40° to +125°C

Use with Part(s)

Description	Part Number
Micro-Fit+ Dual Row Receptacle Housings	<u>206461</u>
Micro-Fit+ Dual Row Plug Housings	<u>215922</u>

This document was generated on Apr 26, 2025