
Data sheet

CB 780/9 NC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



CB cable ties for the fastening of cables and markers.

- They are particularly suitable for fastening CLI M, SFX, WKM and WKS cable markers
- IEC 62275: 2006-conformant
- Fracture-resistant polyamide PA 6.6 with flammability rating V2 to UL-94

General ordering data

Version	Cable ties, 9 x 780 mm, Polyamide 66, 700 N
Order No.	7940006074
Type	CB 780/9 NC
GTIN (EAN)	4032248531202
Qty.	100 items

Downloaded from Arrow.com.

Data sheet

CB 780/9 NC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals	
ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E317499

Dimensions and weights

Depth	1.9 mm	Depth (inches)	0.0748 inch
Height	780 mm	Height (inches)	30.7086 inch
Width	9 mm	Width (inches)	0.3543 inch
Net weight	13.1 g		

Temperatures

Operating temperature range	-40...85 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Installation materials

UV-resistant	No	For re-opening	No
UL 94 flammability rating	V-2	Operating temperature range, max.	85 °C
Operating temperature range, min.	-40 °C	Halogen	No
Cable diameter, max.	233 mm	Basic material	Polyamide 66
Tensile strength	700 N	Bundle diameter, max.	233 mm
Tensile strength (Pound-force)	157 lbf	Bundle diameter, min.	34 mm

Classifications

ETIM 8.0	EC000046	ETIM 9.0	EC000046
ETIM 10.0	EC000046	ECLASS 14.0	27-14-07-02
ECLASS 15.0	27-14-07-02		

Downloaded from Arrow.com.

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



Downloaded from Arrow.com.