




NOTE:

- 1 MATERIAL:
HOUSING: 30% GLASS FILLED PBT, THERMOPLASTIC, BLACK.
CONTACT: PHOS BRONZE
- 2 FINISH: CONTACT PLATING TIN (LEAD FREE); 60 UIN MIN. OVER 30 UIN Ni
SOLDERABILITY :95% COVERAGE MIN.;
WORKING CONDITION:230°±5°C MAX
3. MECHANICAL SPECS:
DURABILITY: 50 CYCLES MIN.
INSERTION FORCE:300 GRAMS MAX.
WITHDRAWAL FORCE: 20 GRAMS MIN.
CONTACT RETENTION: 500 GRAMS MIN.
ACCEPTS: 0.20-0.30 [.008-.012] LEADS
4. ELECTRICAL SPECS:
VOLTAGE RATING: 250V AC,DC
CONTACT RESISTANCE: 20 MILLOHMS MAX.
CURRENT RATING: 1 AMPERE AC,DC
INSULATION RESISTANCE: 1000 MEGOHMS MIN.
DIELECTRIC WITHSTANDING VOLTAGE: AC 1000 V MIN.
5. OPERATING TEMPERATURE: -40°C TO +105°C
- 6 TE LOGO

	32	38.10	40.64	1-2199300-2
FINISH	POS	B±0.15	A±0.20	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN WINNG WANG 18NOV2013	TE Connectivity	
		CHK SIMON LI 18NOV2013		
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME
		0 PLC	± -	DIP SOCKET, 15.24 CENTERLINE OTC STYLE
		1 PLC	± -	
		2 PLC	± 0.2(.008)	
		3 PLC	± -	
		4 PLC	± -	PRODUCT SPEC
		ANGLES	± -	APPLICATION SPEC
MATERIAL		FINISH	WEIGHT	SIZE
			-	A1
CUSTOMER DRAWING		SCALE	5:1	SHEET 1 OF 1