

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories
→ Jumper Bars

General Information

Extended Product Type:	BJS8
Product ID:	1SNA174788R0400
EAN:	3472591747881
Catalog Description:	BJS8-15 Jumper Bars
Long Description:	BJS8 - Jumper Bars - 15 poles - - 8mm Spacing.

Ordering

Minimum Order Quantity:	10 piece
Customs Tariff Number:	85369010

Popular Downloads

Data Sheet, Technical Information:	1SNC160001C0207-CH-J Accessories
Instructions and Manuals:	1SNC160001C0207-CH-J Accessories

Dimensions

Product Net Weight:	3.1 g
----------------------------	-------

Technical

Function:	Jumper Bars
Rated Current (I_n):	Main Circuit 41 A
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Suitable For:	D6/8.ST.RS M6/8.RS M6/8.ST M6/8.STP

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	1SND225001C1009
Instructions and Manuals:	1SNC160001C0207-CH-J Accessories

Classifications

Object Classification Code:	X
ETIM 4:	EC000489 - Cross-connector for terminal block
ETIM 5:	EC000489 - Cross-connector for terminal block

Container Information

Package Level 1 Units:	10 piece
Package Level 1 Gross Weight:	0.031 kg
Package Level 1 EAN:	3472591747881
Package Level 2 Units:	300 piece

