

Step-Down Transformer

APC Symmetra RM 200/100 3.5kVA Step Down Transformer



APC Step-Down Transformer , Input: 200V , Input Connections: NEMA L6-30P , Output Connections: NEMA 5-20R

Includes: Rack Mounting brackets, User Manual

Standard Lead Time : Special Order - Call for Quoted Lead Times

SYTF2J

 [Email Technical Specifications](#)
 [Printer Friendly](#)

- Technical Specifications
- Product Overview
- Documentation
- Options
- Compare Models

Output

Output Connections	(12) NEMA 5-20R	
Overload Protection	Yes	

Input

Nominal Input Voltage	200V	
Input Frequency	50/60 Hz	
Input Connections	NEMA L6-30P	
Number of Power Cords	1	
Load Capacity	3500 VA	

Physical

Net Weight	43.18 KG
Maximum Height	89.00 mm
Maximum Width	483.00 mm
Maximum depth	660.00 mm
Shipping Weight	50.00 KG
Shipping Height	254.00 mm
Shipping Width	622.00 mm
Shipping Depth	953.00 mm
Color	Black

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95%
Operating Elevation	0-3000 meters
Storage Temperature	-25 - 65 °C
Storage Relative Humidity	0 - 95%
Storage Elevation	0-15000 meters

Conformance

Regulatory Approvals	UL 1778
Standard Warranty	2 years repair or replace